

Specification Sheet

Part Number: GT.75X1800



Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

Article Number

854-44384

Type

GT.75X180

Color

Black (BK)

Features & Benefits

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

Quantity Per

bag

Product Description

For custom-cut lengths, HellermannTyton offers the hook and loop strap in various colors in a 5 yard roll and our stand black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot. The Grip Tie is reusable, adjustable, releasable, and easy to install.

Short Description

Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

Global Part Name

GT.75X180

Length L (Imperial)

15.0

Length L (Metric)

4.5

Width W (Imperial)

0.75

Width W (Metric)

19.05

Material

Polyethylene (PE) Polyamide 6 (PA6)

Material Shortcut

PE PA66

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

9606100000

Specification Sheet

Part Number: GT.75X1800



Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

Article Number

854-44384

Type

GT.75X180

Color

Black (BK)

Features & Benefits

- Features quick release for repetitive access to cable and wire.
- Can be opened and closed numerous times without failure.
- Adjustable so one size can accommodate multiple bundle sizes.

Quantity Per

bag

Product Description

For custom-cut lengths, HellermannTyton offers the hook and loop strap in various colors in a 5 yard roll and our stand black up to a 25 yard roll. Ideal for job site applications, desired lengths can be cut on the spot. The Grip Tie is reusable, adjustable, releasable, and easy to install.

Short Description

Grip Tie Roll, 180" Long, .75" Wide, PA6/PP, Black, 1/pkg

Global Part Name

GT.75X180

Length L (Imperial)

15.0

Length L (Metric)

4.5

Width W (Imperial)

0.75

Width W (Metric)

19.05

Material

Polyethylene (PE) Polyamide 6 (PA6)

Material Shortcut

PE PA66

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

1

Package Quantity (Metric)

1

Customs Number

9606100000

