



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## GRP540 5" 40LB Natural CBL Tie *Nsi Industries*

Catalog Number	GRP540
Manufacturer	Nsi Industries
Description	The Powergrp GRP-540 100-Count Resealable Pack Of Type 21 Natural-Colored General-Purpose Cable Ties Are 5" Long, With 40LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 5" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .06" (1.5MM) and 1.3" (33MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and Secur
Weight per unit	0.5050 (lbs/each)
Product Category	Tools & Testers

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Finish	Natural
--------	---------

### Descriptions

Description	5" 40LB NATURAL CBL TIE
extra long description	NSI GRP-540 PowerGRP Cable Tie Natu
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-540 ties combine a self-locking design with a general purpose 40lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-540 ties are waterproof and
Long Description	The PowerGRP GRP-540 100-Count Resealable Pack of Type 21 Natural-Colored General-Purpose Cable Ties are 5" long, with 40lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 5" cables ties around a wide range of equipment with a bundle diameter between .06" (1.5mm) and 1.3" (33mm), using the bent tips and serrated locking mechanism to form an effortless and secur
Product Type	Powergrp Cable Tie Natural 5" 40LB (100PK)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381009081
Manufacturers Part Number	GRP-540
UPC	662381009081

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	1
Package	100
Weight Per each	0.505

## Uses, Certifications, and Standards

standard	UL62275
Temperature Rating	-40F to 185F