



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GRP81200 8" 120LB BLK CBL Tie

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | GRP81200   |
| Manufacturer     | Nsi Industries   |
| Description      | The Powergrp GRP-81200 100-Count Resealable Pack Of Type 21S Ah-2 Black-Colored Heavy-Duty Cable Ties Are 8" Long, With 120LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 8" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between 0.28" (7MM) to 1.97" (50MM) Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and Secur |
| Weight per unit  | 0.6850 (lbs/each)  |
| Product Category | Tools & Testers  |

### Features

|          |        |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 8" 120LB BLK CBL TIE  |
| extra long description | NSI GRP-81200 PowerGRP Cable Tie BI   |
| Features               | PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-81200 ties combine a self-locking design with an industrial strength 120lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-81200 ties are water |
| Long Description       | The PowerGRP GRP-81200 100-Count Resealable Pack of Type 21S AH-2 Black-Colored Heavy-Duty Cable Ties are 8" long, with 120lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 8" cables ties around a wide range of equipment with a bundle diameter between 0.28" (7mm) to 1.97" (50mm) using the bent tips and serrated locking mechanism to form an effortless and secur   |
| Product Type           | Powergrp Cable Tie Black 8" 120LB (100PK)   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381009487 |
| Manufacturers Part Number | GRP-81200      |
| UPC                       | 662381009487   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
|----------------------|--|

## Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 100   |
| Weight Per each | 0.685 |

## Uses, Certifications, and Standards

|                    |              |
|--------------------|--------------|
| standard           | UL62275      |
| Temperature Rating | -40F to 185F |