



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GW335G Gang Mas Box 1/2&3/4KO 71cuin

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | GW335G |
| Manufacturer | Abb Installation Products, Inc |
| Description | Gangable Masonry Box, 71.0 Cubic Inches, 3-3/4 Inches Long X 5-9/16 Inches Wide X 3-1/2 Inches Deep, 1/2 Inch and 3/4 Inch Knockouts, Pre-Galvanized Steel, For Use With Conduit |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | Outlet Boxes, Etc. - Steel |

Features

| | |
|------------------|-------|
| Knockouts | 26 |
| Material | Steel |
| number of outlet | 1 |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Silver |
|-------|--------|

Dimensions and Weight

| | |
|------|--|
| Size | 3-3/4 Inches Length x 5-9/16 Inches Width x 3-1/2 Inches Depth |
|------|--|

Descriptions

| | |
|------------------------|--|
| Description | GANG MAS BOX 1/2&3/4KO 71CUIN |
| extra long description | ABB GW 335 G STL GANGABLE MSNRY BOX |
| Long Description | Gangable Masonry Box, 71.0 Cubic Inches, 3-3/4 Inches Long x 5-9/16 Inches Wide x 3-1/2 Inches Deep, 1/2 Inch and 3/4 Inch Knockouts, Pre-Galvanized Steel, For use with Conduit |
| Product Type | STL Gangable Msnry Box 71.0 Cu-In |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Steel City |
| GTIN | 00785991920963 |
| Manufacturers Part Number | GW 335 G |
| UPC | 785991920963 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | STEEL BOXES & COVERS |
| Type | Masonry Boxes |

Packaging

| | |
|-----------------|-----|
| Carton | 10 |
| Weight Per each | 1.5 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|----------------------|
| Application | For use with conduit |
| standard | UL E2969 / UL E2969 |