



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H0501 STR Male L/T Conn, 1/2", Steel, Ins

Hubbell Wiring Devices

Catalog Number	H0501
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 1/2", Steel, Insulated
Weight per unit	0.1000 (lbs/each)
Product Category	Liquid Tight Fittings

Features

connection	Cap Nut
Material	Steel, Zinc Plated
pallet quantity	14400

Material, Color, and Finish

Color	Metallic
Finish	Metallic

Dimensions and Weight

Length	1.437
Size	1/2 in
Width	1.188

Descriptions

Description	STR MALE L/T CONN, 1/2", STEEL, INS
extra long description	HWDK H0501 STR MALE L/T CONN, 1/2",
Features	Insulated and Non-Insulated Conduit Connectors - Hubbell offers a broad line of metallic liquidtight fittings for use with metallic liq-uidtight conduits and Polytuff I. Hubbell offers trade sizes from 3/8" to 4" in straight, 45°, and 90° body designs. Most connectors are available with either insulated or non-insulated throats. Liquidtight fittings are precision manufactured to exacting standards assuring ease of use and reliability. Straight body 1/2" and 3/4" sizes are list-ed for UL Type 3R, 4, 12 and 13 envi
Long Description	Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 1/2", Steel, Insulated
Product Type	Metallic Liquidtight Fittings
Special Features	Insulated

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585035123
Manufacturers Part Number	H0501
UPC	783585035123



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Metallic Liquidtight Fittings

Packaging

Carton	25
Package	1
Weight Per each	0.1

Uses, Certifications, and Standards

Application	For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit
environmental conditions	Suitable for use in wet locations when a listed sealing ring is used between box and fitting
Mounting	Between Enclosure and Conduit
nema rating	Suitable for use in hazardous locations per Class 1 Div 2
standard	CSA Certified;UL 514B