



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GUAD36 1" Guad Cond Body&CVR

Crouse-Hinds

Catalog Number	GUAD36
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Gua Conduit Outlet Box With Cover, 3" Cover Opening Diameter, Feraloy Iron Alloy, D Shape, 1"
Weight per unit	3.0 (lbs/each)
Product Category	Bodies & Covers

Features

Cable Entry	(2) Side, (1) Down
dimensions	5.5000 IN X 3.3100 IN X 3.5000 IN

Dimensions and Weight

Size	1 in
------	------

Descriptions

Construction	Explosionproof, Dust-Ignitionproof, Raintight
Description	1" GUAD COND BODY&CVR
extra long description	CRS-H GUAD36 1 OUTLET BX 3 CVR FOR
Features	Crouse-Hinds series GUA and GUR explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes. GUA and GUR outlet boxes are certified for Class I, Division 1, Groups B, C, D and Class II, Division 1, Groups E, F, G. GUA boxes are available in ten different hub arrangements, maximizing flexibility in th
Long Description	Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, D shape, 1"
Product Type	1 Outlet BX 3 CVR For THRD Rigid/Imc
Special Features	With Cover, Cover Opening Diameter 3 In

Manufacturer Information

Brand	Eaton
GTIN	00782274463308
Manufacturers Part Number	GUAD36
UPC	782274463308

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting	PAD
standard	UL 886, CSA C22.2