



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2413ST LKG Conn, 20A 125/250V, L14-20R, SPT *Hubbell Wiring Devices*

Catalog Number	HBL2413ST
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Edgeconnect™ Twist-Lock®, Industrial, Female Connector Body, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screwless Terminal, Black and White
Weight per unit	0.4500 (lbs/each)
Product Category	Wiring Devices

Features

connection	EdgeConnect™ Screwless Termination
Material	Nylon
Poles	3
Voltage Rating	125/250

Material, Color, and Finish

Color	Black;White
-------	-------------

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	LKG CONN, 20A 125/250V, L14-20R, SPT
extra long description	HWDK HBL2413ST LKG CONN, 20A 125/25
Features	EdgeConnect™ Screwless Termination system, simply insert the wire and press the plunger down. No tools are required. That connection is fool-proof and long lasting, to all but guarantee a high quality result. Any qualified installer regardless of level of training can guarantee a high quality result.
Long Description	Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Female Connector Body, 20A 125/250V, 3-Pole 4-Wire Grounding, L14-20R, Screwless Terminal, Black and White
Product Type	LKG Conn, 20A 125/250V, L14-20R, SP T
Special Features	EdgeConnect™ Technology, Screwless Termination

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585719115
Manufacturers Part Number	HBL2413ST
series	EdgeConnect™
UPC	783585719115



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	CONNECTOR

Packaging

Carton	1
Package	30
Weight Per each	0.45

Uses, Certifications, and Standards

environmental conditions	IP20 Suitability
Mounting	SCREW
nema rating	I14-20R
standard	Listed to UL 498, Fed.Spec. W-C-596, Certified to CSA C22.2 No.42