



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL2423ST LKG Conn, 20A 3P 250V, L15-20R, B/W, SP** *Hubbell Wiring Devices*

|                  |   |
|------------------|---|
| Catalog Number   | HBL2423ST   |
| Manufacturer     | Hubbell Wiring Devices  |
| Description      | Locking Devices, Edgeconnect™ Twist-Lock®, Industrial, Female Connector Body, 20A 3-Phasedelta 250V Ac, 3-Pole 4-Wire Grounding, L15-20R, Screwless Terminal, Black and White |
| Weight per unit  | 0.4500 (lbs/each)   |
| Product Category | Wiring Devices  |

### **Features**

|                     |                                    |
|---------------------|------------------------------------|
| connection          | EdgeConnect™ Screwless Termination |
| Dielectric Strength | Withstands 3,000V minimum          |
| Material            | Nylon                              |
| Number of Wires     | 4                                  |
| Phase               | 3                                  |
| Poles               | 3                                  |
| Voltage Rating      | 3P 250 VAC                         |

### **Material, Color, and Finish**

|       |                 |
|-------|-----------------|
| Color | Black and White |
|-------|-----------------|

### **Dimensions and Weight**

|      |                        |
|------|------------------------|
| Size | Standard Sized Product |
|------|------------------------|

### **Descriptions**

|                        |   |
|------------------------|---|
| Description            | LKG CONN, 20A 3P 250V, L15-20R, B/W, SP   |
| extra long description | HWDK HBL2423ST LKG CONN, 20A 3P 250   |
| Features               | EdgeConnect™ Screwless Termination system, simply insert the wire and press the plunger down. No tools are required. That connection is fool-proof and long lasting, to all but guarantee a high quality result. Any qualified installer regardless of level of training can guarantee a high quality result. |
| Long Description       | Locking Devices, EdgeConnect™ Twist-Lock®, Industrial, Female Connector Body, 20A 3-PhaseDelta 250V AC, 3-Pole 4-Wire Grounding, L15-20R, Screwless Terminal, Black and White   |
| Product Type           | LKG Conn, 20A 3P 250V, L15-20R, B/W, SP   |
| Special Features       | EdgeConnect™ Technology, Screwless Termination  |

### **Manufacturer Information**

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585719092        |
| Manufacturers Part Number | HBL2423ST             |
| series                    | EdgeConnect™          |
| UPC                       | 783585719092          |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type                 | CONNECTOR   |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 30   |
| Weight Per each | 0.45 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| environmental conditions | IP20 Suitability  |
| Mounting                 | Screw Mount   |
| nema rating              | L15-20R   |
| standard                 | Listed to UL 498, Fed.Spec. W-C-596, Certified to CSA C22.2 No.42 |
| Temperature Rating       | Maximum Continuous 75°C, Minimum -40°C (w/o impact)               |