



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL5669C Conn, 15A 250V, 6-15R, B/W** *Hubbell Wiring Devices*

Catalog Number	HBL5669C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 250V, 6-15R, Black and White, Single Pack.
Weight per unit	0.0820 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	15
connection	Screw Terminals
Current Rating	15
insulation	Insulated Body
Material	Nylon
Number of Conductors	3-Wire Grounding
pallet quantity	4000
Poles	2-Pole
Voltage Rating	250

### **Material, Color, and Finish**

Color	Black;White
-------	-------------

### **Dimensions and Weight**

Size	2.78 in x 1.53 in x 1.53 in
------	-----------------------------

### **Descriptions**

Description	CONN, 15A 250V, 6-15R, B/W
extra long description	HWDK HBL5669C CONN, 15A 250V, 6-15R
Long Description	Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 250V, 6-15R, Black and White, Single Pack.
Product Type	Conn, 15A 250V, 6-15R, B/W
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585175805
Manufacturers Part Number	HBL5669C
series	Insulgrip®
UPC	783585175805



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Connector Body

## Packaging

Carton	1
Package	10
Weight Per each	0.082

## Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	6-15R
standard	CSA Certified to C22.2 No. 42 File 280;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706