



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL5966VBLK Valise Plug, 15A 125V, 5-15P, Insul-D, BK** *Hubbell Wiring Devices*

Catalog Number	HBL5966VBLK
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Black, Single Pack.
Weight per unit	0.1000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	15
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	15
Material	Polycarbonate
Number of Wires	3-Wire
pallet quantity	6000
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	1875;1875.0000
Wire Size	#18 to #16

### **Dimensions and Weight**

Size	Standard Sized
------	----------------

### **Descriptions**

Description	VALISE PLUG, 15A 125V, 5-15P, INSUL-D,BK
extra long description	HWDK HBL5966VBLK VALISE PLUG, 15A 1
Long Description	Straight Blade Devices, Male Plug, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Black, Single Pack.
Product Type	Valise Plug, 15A 125V, 5-15P, Insul-D, BK
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585013428
Manufacturers Part Number	HBL5966VBLK
series	Valise®
UPC	783585013428



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG

## Packaging

Carton	1
Package	10
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	Industrial/Commercial Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	5-15P
standard	CSA Certified to C22.2 No. 42 File 280;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706