



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL9330 RCPT, 2P3W, 30A 250V, 6-30R, BK *Hubbell Wiring Devices*

Catalog Number	HBL9330
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, RTP, Industrial Grade, 2-Pole 3-Wire Grounding, 30A 250V, 6-30R, Black, Single Pack.
Weight per unit	0.4000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Back and Side Wired Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Material	Thermoplastic/Composite
Number of Wires	3-Wire Grounding
pallet quantity	2560
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	7,500
Wire Size	#12 to #4

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	3.28 in x 2.25 in x 2.23 in
------	-----------------------------

Descriptions

Description	RCPT, 2P3W, 30A 250V, 6-30R, BK
extra long description	HWDK HBL9330 RCPT, 2P3W, 30A 250V,
Long Description	Straight Blade Devices, Receptacles, RTP, Industrial Grade, 2-Pole 3-Wire Grounding, 30A 250V, 6-30R, Black, Single Pack.
Product Type	RCPT, 2P3W, 30A 250V, 6-30R, BK
Special Features	Standard

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015231
Manufacturers Part Number	HBL9330
series	Extra Heavy Duty
UPC	783585015231



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	RECEPTACLE

Packaging

Carton	1
Package	10
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	6-30R
standard	CSA Certified;NEMA® WD-6 Compliant;UL Listed File E2186