



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL9431C Plug, 3P4W, 30A 125/250V, 14-30P** *Hubbell Wiring Devices*

Catalog Number	HBL9431C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Male Plug, Nylon, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 4-Wire Grounding, 30A 125/250V, 14-30P, Black, Single Pack.
Weight per unit	0.8500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	30
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	30
Material	Nylon
Number of Wires	4-Wire
pallet quantity	765
Phase	1
Poles	3-Pole
Voltage Rating	125/250;125 V V
Wattage	7
Wire Size	#12 to #4

### **Material, Color, and Finish**

Color	Black
-------	-------

### **Dimensions and Weight**

Size	4.13 in x 2.88 in x 2.88 in
------	-----------------------------

### **Descriptions**

Description	PLUG, 3P4W, 30A 125/250V, 14-30P
extra long description	HWDK HBL9431C PLUG, 3P4W, 30A 125/2
Long Description	Straight Blade Devices, Male Plug, Nylon, Heavy Duty, Industrial/Commercial Grade, Straight, 3-Pole 4-Wire Grounding, 30A 125/250V, 14-30P, Black, Single Pack.
Product Type	Plug, 3P4W, 30A 125/250V, 14-30P
Special Features	Straight



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015309
Manufacturers Part Number	HBL9431C
series	Extra Heavy Duty
UPC	783585015309

## Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG

## Packaging

Carton	1
Package	5
Weight Per each	0.85

## Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	14-30P
standard	Certified to CSA;UL Listed File E1706