



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HCLR25 25A 600V Class CC Fast Acting Fuse

*Edison Fuses*

Catalog Number	HCLR25
Manufacturer	Edison Fuses
Description	Eaton Edison HCLR Fuse, 25 A, Class CC, Non-Indicating, 200 Kaic, Standard, 10, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Renewable & Non-Renewable

### Features

amperage rating	25 A
amps	25
class	Class CC
dimensions	1.0000 IN X 0.4060 IN X 0.4060 IN
Fuse Type	Class CC Fast Acting Fuses
interrupt rating	200 kAIC
Voltage	600V
Voltage Rating	600 V

### Descriptions

Description	25A 600V CLASS CC FAST ACTING FUSE
extra long description	MOR T626-HCLR25 HCLR25 Fast Acting
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Long Description	Eaton Edison HCLR fuse, 25 A, Class CC, Non-indicating, 200 kAIC, Standard, 10, 600 V
Product Type	HCLR25 Fast Acting 600V/25a
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton
GTIN	00782634420729
Manufacturers Part Number	HCLR25
UPC	782634420729



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

## Packaging

Carton	1
Package	10
Weight Per each	0.02

## Uses, Certifications, and Standards

Application	Datacenters - Facilities: Critical Power
standard	UL Listed,CSA Certified,CE Marked,RoHS Compliant