



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HCTR2.5 2-1/2A 600V Class CC Time Delay Small Control Fuse

*Edison Fuses*

|                  |   |
|------------------|---|
| Catalog Number   | HCTR2.5   |
| Manufacturer     | Edison Fuses  |
| Description      | Eaton Edison HCTR Fuse, Current-Limiting High Inrush Time-Delay Fuse, Rejection Style, 2.5 A, Class CC, Non-Indicating, 12 Sec At 200%, 200 Kaic, Nickel-Plated Brass Endcaps, Melamine Tube, Standard, 10, 600 V |
| Weight per unit  | 0.1000 (lbs/each)   |
| Product Category | Dual Element  |

### Features

|                  |  |
|------------------|--|
| amperage rating  | 2.5  |
| amps             | 2.5  |
| dimensions       | 1.0000 IN X 0.4060 IN X 0.4060 IN            |
| Fuse Class       | Class CC                                     |
| Fuse Type        | Class CC Time Delay Fuses - Control Circuits |
| interrupt rating | 200 kAIC                                     |
| Material         | Melamine Tube; Nickel-plated brass endcaps   |
| Voltage          | 600V   |
| Voltage Rating   | 600 V  |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 2-1/2A 600V CLASS CC TIME DELAY SMALL CONTROL FUSE  |
| extra long description | BUSS HCTR2.5 UL CLASS CC TIME DELAY   |
| Features               | Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection. |
| Long Description       | Eaton Edison HCTR fuse, Current-limiting high inrush time-delay fuse, Rejection style, 2.5 A, Class CC, Non-indicating, 12 sec at 200%, 200 kAIC, Nickel-plated brass endcaps, Melamine tube, Standard, 10, 600 V   |
| Product Type           | UI Class CC Time Delay  |
| Special Features       | Rejection Style   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782634802174 |
| Manufacturers Part Number | T626-HCTR2.5   |
| UPC                       | 782634802174   |

## Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | MIDGET FUSES |
| Type                 | FUSE         |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 10  |
| Weight Per each | 0.1 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Safety and Security Systems |
| standard    | RoHS Compliant,CE Marked   |