



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL5661 SGL RCPT, Ind GRD, 15A 250V, 6-15R, BR *Hubbell Wiring Devices*

| | |
|------------------|--|
| Catalog Number | HBL5661 |
| Manufacturer | Hubbell Wiring Devices |
| Description | Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack |
| Weight per unit | 0.1500 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|---------------------|---------------------------|
| amperage rating | 15 |
| connection | Back and Side Wired |
| Current Rating | 15 |
| Dielectric Strength | Withstands 2,000V minimum |
| Number of Wires | 3-Wire |
| pallet quantity | 5500 |
| Phase | 1 |
| Poles | 2-Pole |
| Voltage Rating | 250 V |
| Wattage | 3,750 |
| Wire Size | #12 to #10 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Brown |
|-------|-------|

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | 1.94 in x 1.63 in x 1.19 in |
|------|-----------------------------|

Descriptions

| | |
|------------------------|--|
| Description | SGL RCPT, IND GRD, 15A 250V, 6-15R, BR |
| extra long description | HWDK HBL5661 SGL RCPT, IND GRD, 15A |
| Long Description | Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack |
| Product Type | SGL RCPT, Ind GRD, 15A 250V, 6-15R, BR |
| Special Features | Standard |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585013992 |
| Manufacturers Part Number | HBL5661 |
| series | Extra Heavy Duty |
| UPC | 783585013992 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Industrial receptacles |
| Type | SINGLE RECEPTACLE |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.15 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Extra Heavy Duty |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| nema rating | 6-15R |
| standard | Certified to CSA 22.2, No. 42 File 285;Guide RTRT Fed Spec WC596G;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186 |