



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBLDS60 NM Sloped Disc, 60A Unfused, 4X *Hubbell Wiring Devices*

Catalog Number	HBLDS60
Manufacturer	Hubbell Wiring Devices
Description	Industrial Grade, Motor Disconnect Switch, Unfused, 3 Pole, 60A 600V Ac, Screw Terminals, IP69K, Nema Type 4X, 12 Non-Metallic Sloped Top Enclosure, Culus, NSF, Ce, UI 508 / UI 60947-4-1a
Weight per unit	6.1 (lbs/each)
Product Category	20240715143619

### Features

operating cycles	10,000
------------------	--------

### Descriptions

Description	NM SLOPED DISC, 60A UNFUSED, 4X
extra long description	HWDK HBLDS60 NM SLOPED DISC, 60A UN
Features	NEC section 430.102(B) requires each motor controller to have a disconnect within line of sight from the motor and driven equipment. Hubbell's Circuit-Lock® Unfused Disconnect Switches are UL listed as a manual motor controller and also "suitable as a motor disconnect" and meet these code requirements.
Long Description	Industrial Grade, Motor Disconnect Switch, Unfused, 3 Pole, 60A 600V AC, Screw Terminals, IP69k, NEMA Type 4X, 12 Non-Metallic Sloped Top Enclosure, cULus, NSF, CE, UL 508 / UL 60947-4-1A
Product Type	NM Sloped Disc, 60A Unfused, 4X

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585763224
Manufacturers Part Number	HBLDS60
series	Non-Fused
UPC	783585763224

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Disconnect Switches

### Packaging

Carton	1
Package	0
Weight Per each	6.05



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial and/or Washdown
Enclosure	IP69k and UL Type 4X, 12
environmental conditions	Indoor and Outdoor
standard	cULus Listed