



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HFD3025 Type HFD 3P 25A Trip 600V Class 65KA At 480V No

Eaton Corp

Catalog Number	HFD3025
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, HFD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 25 A, 600 Vac, 250 VDC, Load Side, 50/60 HZ
Weight per unit	4.4 (lbs/each)
Product Category	3 Pole

Features

Current Rating	25 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
frame	F
media	Yes
Poles	3
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE HFD 3P 25A TRIP 600V CLASS 65KA AT 480V NO
extra long description	ETN HFD3025 HFD 3P 25A TRIP 600V CL
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 25 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz
Product Type	HFD 3P 25A Trip 600V Class 65KA 480V No

Manufacturer Information

Brand	Eaton
GTIN	00786679175828
Manufacturers Part Number	HFD3025
UPC	786679175828

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.35

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed