



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

445 Texas Avenue  
78664-2138, TX Round Rock  
Phone: 512-246-8001  
Fax: 512-246-8002



## HLBSL4069FS231EM \*Phase Out\* 4" Led Trim 27K/3K/35K Ultra Thin Lite *Cooper Lighting Solutions*

Catalog Number	HLBSL4069FS231EM
Manufacturer	Cooper Lighting Solutions
Description	4-Inch Led Smooth Lens Downlight With Plastic Housing and Remote Driver / Junction Box With Selectable CCT (2700K-3500K)
Weight per unit	0.5100 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.085 A at 120 V
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120V
Wattage	10 W

### Material, Color, and Finish

Finish	white
Style	(blank)

### Descriptions

Description	*PHASE OUT* 4" LED TRIM 27K/3K/35K ULTRA THIN LITE
extra long description	CLS HLBSL4069FS231EMWR 4" RD SFT LE
Long Description	4-Inch LED smooth lens downlight with plastic housing and remote driver / junction box with Selectable CCT (2700K-3500K)
Product Type	4" RD SFT Lens, 600LM, 27-35K, 120V, MW
Special Features	Features a round polymer trim and smooth lens

### Manufacturer Information

Brand	HALO
GTIN	00080083912346
Manufacturers Part Number	HLBSL4069FS231EMWR
UPC	080083912346

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLBSL Smooth Lens Downlight

### Packaging

Carton	1
Package	4
Weight Per each	0.51



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

445 Texas Avenue  
78664-2138, TX Round Rock  
Phone: 512-246-8001  
Fax: 512-246-8002

## Uses, Certifications, and Standards

Application	lighting
Mounting standard	Direct Mount Energy Star Certified;IECC Compliant;Title 24 Compliant;UL Certified - Damp Location;RoHS Compliant;Showerlight;AIR-TITE (TM) Certified ASTM E283;Wet Locations Listed;LM79/LM80 Compliant;EMI/RFI per FCC 47CFR Part 15 B;California Title 24;IP44 Rated