

Eaton HPC4046SHLG

Catalog Number: HPC4046SHLG

Eaton Cutler-Hammer series Housing panel, 400A, 120/240V, BRH/BWH Secondary Circuit, Aluminum Bus Material, Lever bypass, NEMA 3R Enclosure, Overhead/underground Feed Type, 22 kAIC Interrupt Rating, Surface mounting, Ringless Security

General specifications



Product Name

Eaton house panel

Catalog Number

HPC4046SHLG

UPC

786685271019

Product Length/Depth

7.75 in

Product Height

46 in

Product Width

33 in

Product Weight

123 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

House panel

Utility approvals

GA : Georgia Power

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : Dominion

VA : Dominion

Interrupt rating

10 kAIC

Enclosure

NEMA 3R

Secondary circuit breaker

BRH/BWH

Amperage Rating

400 A

Line

Lug landings for compression, lugs not included

Mounting

Surface

Number of spaces

4

Security

Ringless

Voltage rating

120/240 V

Number of sockets

1

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - 400A METER BREAKER HPC30SHL, HPC40SHL, HPC4046SHLG, HPC4046SHLGX](#)

Specifications and datasheets

[Eaton Specification Sheet - HPC4046SHLG](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

Used with

Type BR breakers

Bypass

Lever

Number of circuits

6

Bus material

Aluminum

Feed type

Top/bottom

Main circuit breaker

CSR2200



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)