



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IOPA4P32N35I 4LT T8 Bal

*Advance By Signify*

Catalog Number	IOPA4P32N35I
Manufacturer	Advance By Signify
Description	The Right Choice For A Broad Range Of New Construction and Retrofit Applications Compatible With Energy Saving Lamps;Eligible For Utility Rebates;Maximizes Fixture Design;Reduces Packaging Waste Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology. Intellivolt (120-277V) Input Voltage Range;Lamp Striation Reduction;Meets Nema Premium/Cee;Smallest Enclosure In Industry General Office Lighting, Institutional, Gover
Weight per unit	0.8000 (lbs/each)
Product Category	Electronic Linear Fluorescent

### Features

Ballast Factor	0.87
Lamp Type	T8
Number of Lamps	4
Power Factor	0.98
start type	Instant Start
total harmonic distortion	10
Voltage Rating	120-277
Wattage	32
Wire Type	SOLID

### Material, Color, and Finish

Housing Material	Metal
------------------	-------

### Dimensions and Weight

Height	3.94
Width	5.12



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	4LT T8 BAL
extra long description	ADV 498857 ELE BALLAST (4) F32T8 12
Long Description	The right choice for a broad range of new construction and retrofit applications Compatible with Energy Saving lamps;Eligible for Utility Rebates;Maximizes fixture design;Reduces packaging waste Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology. IntelliVolt (120-277V) input voltage range;Lamp Striation Reduction;Meets NEMA Premium/CEE;Smallest enclosure in industry General office lighting, institutional, gover
Product Type	Ele Ballast (4) F32T8 120-277V
Special Features	UL, CSA, NEMA Premium, RoHS

## Manufacturer Information

Brand	Signify Electronics
GTIN	00781087115244
Manufacturers Part Number	498857
UPC	781087115244

## Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Electronic Fluorescent

## Packaging

Carton	1
Package	10
Weight Per each	0.8

## Uses, Certifications, and Standards

Frequency Rating	50to60
standard	CSA certificate;UL certificate;CEC Listing;CEE Rated;NEMA Premium;RoHS Compliant