



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG5362I Dup RCPT, Ig, 20A 125V, 5-20R, Iv *Hubbell Wiring Devices*

Catalog Number	IG5362I
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Isolated Ground, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2,500
Wire Size	#12 to #10

Dimensions and Weight

Size	3.28 in x 1.33 in x 1.05 in
------	-----------------------------

Descriptions

Description	DUP RCPT, IG, 20A 125V, 5-20R, IV
extra long description	HWDK IG5362I DUP RCPT, IG, 20A 125V
Features	<p>In February 1968, Hubbell patented the first isolated ground receptacle. Today - when a clean, noise-free ground is more important than ever—Hubbell is still setting the standard. Hubbell uses insulation barrier construction on many models to isolate the ground contacts from the mounting strap. The green grounding screw is connected directly to the grounding contacts. In this way, ground contacts are separated from the mounting strap and also from the conventional grounding system. The isolated ground circ</p>
Long Description	Straight Blade Isolated Ground, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R
Product Type	Dup RCPT, Ig, 20A 125V, 5-20R, Iv
Special Features	Isolated Ground



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585876887
Manufacturers Part Number	IG5362I
series	Heavy Duty
UPC	783585876887

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Standard Duplex

Packaging

Carton	1
Package	10
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Extra Heavy Duty Specification Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42 File 285;Fed. Spec. WC596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186