



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IZT3PSP32SC35I 277V Bal

Advance By Signify

Catalog Number	IZT3PSP32SC35I
Manufacturer	Advance By Signify
Description	Maximum Dimming Versatility Compatible With Controls From Numerous Manufacturers Using Standard 0-10VDC Controls; Ideal For Frequent Switching Applications Such As Occupancy Sensors and Daylight Harvesting - Programmed Start Operation The Mark 7 0-10V Series Of Dimmable Electronic Ballasts Offer Maximum Versatility By Incorporating Separate Control Leads For Use With A Wide Array Of Controllers, Including Occupancy Sensors, Daylight Harvesting Controls, and Building Management Systems From More Than 40 Manu
Weight per unit	1.0 (lbs/each)
Product Category	20140826095128

Features

Ballast Factor	1.00
dimnable	Yes
Lamp Type	T8 RS
Number of Lamps	3
Power Factor	0.99
Power Rating	32
start type	Programmed Start
Voltage Rating	120-277

Dimensions and Weight

Height	4.65
Length	3.74
Width	6.69

Descriptions

Description	277V BAL
extra long description	ADV 503698 ELE DIMMING BALLAST(3)F3
Long Description	Maximum dimming versatility Compatible with controls from numerous manufacturers using standard 0-10VDC controls; Ideal for frequent switching applications such as occupancy sensors and daylight harvesting - Programmed start operation The Mark 7 0-10V series of dimmable electronic ballasts offer maximum versatility by incorporating separate control leads for use with a wide array of controllers, including occupancy sensors, daylight harvesting controls, and building management systems from more than 40 manu
Product Type	Ele Dimming Ballast(3)F32T8 120-277V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Advance
GTIN	00781087135396
Manufacturers Part Number	503698
UPC	781087135396

Taxonomies, Classifications, and Categories

Category Description	DIMMING BALLASTS
----------------------	------------------

Packaging

Carton	1
Weight	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Lighting Luminaire Component
Frequency Rating	50to60
standard	UL certificate;CEC Listing;CEE Rated;NEMA Premium;RoHS Compliant;CSA certificate