



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



J20009NE Lineman'S Pliers, 9" , Journeyman Handle

Klein Tools

| | |
|------------------|--|
| Catalog Number | J20009NE |
| Manufacturer | Klein Tools |
| Description | Heavy Duty Side Cutting Plier, Steel Blade Material, 25/32 In Blade Length, Light Blue/Black (Handle), Journeyman (Handle), 9-1/2 In Overall Length, 1-19/32 In Jaw Length, 1-1/4 In Jaw Width, 1.1 LB |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|----------------|-----------------|
| Handle Length | 5.55" (14.1 cm) |
| jaw thickness | 0.613" (1.6 cm) |
| knife length | 0.797" (2 cm) |
| Material | Steel |
| media | Yes |
| Overall Height | 0.75" (1.9 cm) |
| Overall Width | 2.13 (5.4 cm) |
| tether capable | No |

Material, Color, and Finish

| | |
|--------------|------------------|
| Handle Color | LIGHT BLUE/BLACK |
|--------------|------------------|

Descriptions

| | |
|------------------------|--|
| Also Known As... | Pliers |
| | Loppers |
| | Linesman's Pliers |
| | Rabbit Ears |
| | Diagonal cutters |
| Description | LINEMAN'S PLIERS, 9" , JOURNEYMAN HANDLE |
| extra long description | KLEIN J2000-9NE Pliers, Heavy Duty |
| similar brands | kleins |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00092644721021 |
| UPC | 092644721021 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | HAND TOOLS |
| Type | Side Cutting Pliers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 3 |
| Weight Per each | 1.13 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | ACSR, Screws, Nails, Most Hardened Wire |
|-------------|---|