



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## JDL175 175A 600V Class J Time Delay Fuse

*Edison Fuses*

Catalog Number	JDL175
Manufacturer	Edison Fuses
Description	Eaton Edison Series JDL Fuse, Time-Delay Current-Limiting Fuse, Non-Indicating, 175 A, Class J, 200 Kaic, Standard, 5, 600 V
Weight per unit	0.8000 (lbs/each)
Product Category	Dual Element

### Features

amperage rating	175 A
amps	175
class	Class J
dimensions	5.7500 IN X 1.6300 IN X 1.6300 IN
Fuse Type	Class J Time Delay Fuses
interrupt rating	200 kAIC
media	Yes
Voltage	600V
Voltage Rating	600 V

### Descriptions

Description	175A 600V CLASS J TIME DELAY FUSE
extra long description	MOR T626-JDL175 Class J Time Delay
Features	Edison's UL Class J fuse products are offered in both Dual-Element Time-Delay (JDL) and Fast-Acting (JFL) types. Both types have 200,000 amp interrupting rating at 600Vac RMS Sym amps. Their small physical size and high performance characteristics makes Class J fuses ideal for any space-limited applications. Edison's JFL fuses are best suited for the protection of non-inductive loads such as resistive heating and lighting circuits.
Long Description	Eaton Edison series JDL fuse, Time-delay current-limiting fuse, Non-indicating, 175 A, Class J, 200 kAIC, Standard, 5, 600 V
Product Type	Class J Time Delay Fuses 600V 175a
Special Features	Non-Indicating

### Manufacturer Information

Brand	Eaton
GTIN	00782634803539
Manufacturers Part Number	JDL175
UPC	782634803539



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description Fuses & Fuse Accessories

Type FUSE

## Packaging

Carton 1

Weight Per each 0.8

## Uses, Certifications, and Standards

Application Datacenters - Facilities: Critical Power

standard CSA Certified,UL Listed,RoHS Compliant,CE Marked