



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



K125 1-1/4" & 1-1/2" Alu FM5 Cond Body CVR Appleton/Oz Gedney

Catalog Number	K125
Manufacturer	Appleton/Oz Gedney
Description	Form 85 Unilets Blank Cover With Screw, Hub Size: 1-1/4 - 1-1/2 In, Form: 85, Mounting: Screw-In, Material: Stamped Aluminum, Finish: Natural Aluminum, Standard: UI 514A, UI 514B, UI File Number E2527, Csa C22.2 No. 18.3, Csa 065183, Nema FB-1, For Form 85 Unilet Conduit Outlet Bodies
Weight per unit	0.1400 (lbs/each)
Product Category	Alum

Features

Form	85
------	----

Material, Color, and Finish

Finish	Natural Aluminum
--------	------------------

Dimensions and Weight

Hub Size	1-1/4 - 1-1/2
----------	---------------

Descriptions

extra long description	APP K125&150-A 1-1/4&1-1/2 COVER FO
Long Description	Form 85 UNILETS Blank Cover With Screw, Hub Size: 1-1/4 - 1-1/2 IN, Form: 85, Mounting: Screw-In, Material: Stamped Aluminum, Finish: Natural Aluminum, Standard: UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1, For Form 85 Unilet Conduit Outlet Bodies
Product Type	1-1/4&1-1/2 Cover For Form 35
Special Features	Domed to provide extra wiring space;Stainless steel fastening screws;Wiring capacity: 2.5 CU-IN as per NEC 314.16(A)

Manufacturer Information

Brand	Appleton
GTIN	00781381471008
Manufacturers Part Number	K125&150-A
UPC	781381471008

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Blank Cover With Screw

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 0.14

Uses, Certifications, and Standards

Application For Form 85 Unilet Conduit Outlet Bodies

Mounting Screw-In

standard UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3,
CSA 065183, NEMA FB-1