

Specifications



Eaton KRP-C-800SP

Eaton Bussmann Series Class L fuse, KRP-C, time-delay, current limiting fuse, 800 A, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc

General specifications

PRODUCT NAME	Eaton Bussmann series KRP-C fuse
CATALOG NUMBER	KRP-C-800SP
UPC	051712605083
PRODUCT LENGTH/DEPTH	8.63 in
PRODUCT HEIGHT	2.53 in
PRODUCT WIDTH	2.53 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	800 A
INTERRUPT RATING	300 kAIC at 600 Vac 100 kA at 300 kAIC Vdc
RESPONSE TIME	4 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

General information

CLASS	Class L
CONNECTION	Bolted blade end x bolted blade end
FUSE INDICATOR	Non-indicating
SPECIAL FEATURES	Small footprint

Physical details

PACKAGING TYPE	Standard
----------------	----------

Resources

CATALOGS	Bussmann Full Line Catalog Low Voltage Branch Circuit Fuse Chapter
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	Bussmann series Fuseology
TECHNICAL DATA SHEETS	Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Eaton KRP-C-800SP

Eaton Bussmann Series Class L fuse, KRP-C, time-delay, current limiting fuse, 800 A, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc

General specifications

PRODUCT NAME	Eaton Bussmann series KRP-C fuse
CATALOG NUMBER	KRP-C-800SP
UPC	051712605083
PRODUCT LENGTH/DEPTH	8.63 in
PRODUCT HEIGHT	2.53 in
PRODUCT WIDTH	2.53 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant

Electrical rating

AMPERAGE RATING	800 A
INTERRUPT RATING	300 kAIC at 600 Vac 100 kA at 300 kAIC Vdc
RESPONSE TIME	4 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

General information

CLASS	Class L
CONNECTION	Bolted blade end x bolted blade end
FUSE INDICATOR	Non-indicating
SPECIAL FEATURES	Small footprint

Physical details

PACKAGING TYPE	Standard
----------------	----------

Resources

CATALOGS	Bussmann Full Line Catalog Low Voltage Branch Circuit Fuse Chapter
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	Bussmann series Fuseology
TECHNICAL DATA SHEETS	Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

