



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KL641 A:4/0, B:3-4 Alu Comp Splice

Abb Installation Products, Inc

Catalog Number	KL641
Manufacturer	Abb Installation Products, Inc
Description	Aluminum 3-1/2 Inch Service Entrance Compression Splice For Wire Range - End A: 4/0 Ascr, 4/0 STR., Orange, End B: 4 Ascr, 3-4 STR., 2 Sol., Orange, Die: 840. For Al to Al and Al to Cu Conductors.
Weight per unit	0.0630 (lbs/each)
Product Category	Large Terminals & Connectors

Features

connection	Compression
insulation	None
Material	Aluminum
Number of Conductors	2

Dimensions and Weight

Size	3-1/2 Inch
------	------------

Descriptions

Description	A:4/0,B:3-4 ALU COMP SPLICE
extra long description	ABB KL64-1 AL SERVENTR SPLICE A:4/0
Long Description	Aluminum 3-1/2 Inch Service Entrance Compression Splice for Wire Range - End A: 4/0 ASCR, 4/0 Str., Orange, End B: 4 ASCR, 3-4 Str., 2 Sol., Orange, Die: 840. For AL to AL and AL to CU Conductors.
Product Type	Al Serventr Splice A:4/0 B:3-4 3.5
Special Features	Splices large conductors required for commercial service, use as low cost reducing sleeve. All sizes can be installed with popular mechanical and hydraulic tools. Center stop assures proper conductor positioning. Quick identifications with color-coded foil caps

Manufacturer Information

Brand	Blackburn Mechanical
GTIN	00783786050109
Manufacturers Part Number	KL64-1
UPC	783786050109

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Compression Splice Service Entrance



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Package	250
Weight Per each	0.063

Uses, Certifications, and Standards

Application	For Combinations of Aluminum-to-Aluminum and Aluminum-to-Copper Conductors
environmental conditions	All Seasons / Conditions
Mounting	None
standard	Passes the requirements of ANSI C119.4