

Eaton KRP-C-1200SP

Catalog Number: KRP-C-1200SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 1200 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V, 100 kAIC Vdc, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series KRP-C fuse	KRP-C-1200SP
UPC	Product Length/Depth
051712605120	10.75 in
Product Height	Product Width
2.78 in	2.78 in
Product Weight	Warranty
0.001 lb	Not Applicable

Compliances

CE Marked
RoHS Compliant

Electrical rating

Amperage Rating

1200 A

Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

Response time

4 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Packaging type

Standard

General information

Class

Class L

Connection

Bolted blade end x bolted blade end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann Full Line Catalog](#)

[Low Voltage Branch Circuit Fuse Chapter](#)

Compliance information

[RoHS Search Tool](#)

Multimedia

[Bussmann series Fuseology](#)

Technical data sheets

[Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton KRP-C-1200SP

Catalog Number: KRP-C-1200SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 1200 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V, 100 kAIC Vdc, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series KRP-C fuse	KRP-C-1200SP
UPC	Product Length/Depth
051712605120	10.75 in
Product Height	Product Width
2.78 in	2.78 in
Product Weight	Warranty
0.001 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical rating

Amperage Rating

1200 A

Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

Response time

4 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Packaging type

Standard

General information

Class

Class L

Connection

Bolted blade end x bolted blade end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann Full Line Catalog](#)

[Low Voltage Branch Circuit Fuse Chapter](#)

Compliance information

[RoHS Search Tool](#)

Multimedia

[Bussmann series Fuseology](#)

Technical data sheets

[Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)