

# Eaton KRP-C-1600SP

Catalog Number: KRP-C-1600SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 1600 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V, 100 kAIC Vdc, 600 V, 300 Vdc



## General specifications

|                                  |                      |
|----------------------------------|----------------------|
| Product Name                     | Catalog Number       |
| Eaton Bussmann series KRP-C fuse | KRP-C-1600SP         |
| UPC                              | Product Length/Depth |
| 051712605168                     | 10.75 in             |
| Product Height                   | Product Width        |
| 3.03 in                          | 3.03 in              |
| Product Weight                   | Warranty             |
| 5.72 lb                          | Not Applicable       |

## Compliances

CE Marked  
RoHS Compliant

## Electrical rating

### Amperage Rating

1600 A

### Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

### Response time

4 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Packaging type

Standard

## General information

### Class

Class L

### Connection

Bolted blade end x bolted blade end

### Fuse indicator

Non-indicating

## Resources

### Catalogs

[Bussmann Full Line Catalog](#)

[Low Voltage Branch Circuit Fuse Chapter](#)

### Compliance information

[RoHS Search Tool](#)

### Multimedia

[Bussmann series Fuseology](#)

### Technical data sheets

[Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton KRP-C-1600SP

Catalog Number: KRP-C-1600SP

Eaton Bussmann series KRP-C fuse, Current-limiting time-delay fuse, 1600 A, L, Non-indicating, Bolted blade end x bolted blade end, 4 sec at 500%, 300 kAIC at 600 V, 100 kAIC Vdc, 600 V, 300 Vdc



## General specifications

|                                  |                      |
|----------------------------------|----------------------|
| Product Name                     | Catalog Number       |
| Eaton Bussmann series KRP-C fuse | KRP-C-1600SP         |
| UPC                              | Product Length/Depth |
| 051712605168                     | 10.75 in             |
| Product Height                   | Product Width        |
| 3.03 in                          | 3.03 in              |
| Product Weight                   | Warranty             |
| 5.72 lb                          | Not Applicable       |

## Compliances

CE Marked  
RoHS Compliant

## Electrical rating

### Amperage Rating

1600 A

### Interrupt rating

300 kAIC at 600 Vac

100 kAIC Vdc

### Response time

4 sec at 500%

### Voltage rating

600 Vac, 300 Vdc

## Physical details

### Packaging type

Standard

## General information

### Class

Class L

### Connection

Bolted blade end x bolted blade end

### Fuse indicator

Non-indicating

## Resources

### Catalogs

[Bussmann Full Line Catalog](#)

[Low Voltage Branch Circuit Fuse Chapter](#)

### Compliance information

[RoHS Search Tool](#)

### Multimedia

[Bussmann series Fuseology](#)

### Technical data sheets

[Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)