



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

L10.5T848G830DX2 10.5W Led T8 48" 30K Singl/DBL Ended 1700LM Glass *Keystone Technologies*



| | |
|------------------|---|
| Catalog Number | L10.5T848G830DX2 |
| Manufacturer | Keystone Technologies |
| Description | 10.5W Led T8 Tube, Glass Construction, 120-277V Input, 4 FT., 3000K, Direct Drive, Single or Double Ended |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 1650 |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 10.5 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 3000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Glass |
| Description | 10.5W LED T8 48" 30K SINGL/DBL ENDED 1700LM GLASS |
| extra long description | Key KT-LED10.5T8-48G-830-DX2 /G2-CP |
| Long Description | 10.5W LED T8 Tube, Glass Construction, 120-277V Input, 4 ft., 3000K, Direct Drive, Single or Double Ended |
| Product Type | 10.5W Led T8 Tube, Glass Construction, 120-277V Input, 4 FT. |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | Keystone |
| GTIN | 00843654132891 |
| Manufacturers Part Number | KT-LED10.5T8-48G-830-DX2 /G2-C |
| UPC | 843654132891 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|-----|
| Carton | 25 |
| Weight Per each | 0.7 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|