



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTSR15 15A 600V Fa Class RK1 Fuse *Bussmann Fuses*

Catalog Number	KTSR15
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class RK1 Fuse, KTS-R, Fast-Acting, Current Limiting Fuse, 15 A, Rejection Style Fuse, Interrupting Rating Of 200 Ka At 600 Vac
Weight per unit	0.1500 (lbs/each)
Product Category	Renewable & Non-Renewable

Features

amperage rating	15
class	Class RK1
connection	Ferrule End X Ferrule End
dimensions	0.8000 IN X 0.8000 IN X 5.0000 IN
element	Single
Fuse Class	Class RK1
interrupt rating	200 kAIC at 600 Vac
Material	Melamine Tube
media	Yes
Voltage Rating	600 V

Dimensions and Weight

Size	0.81 In Diameter X 5.00 In Length
------	-----------------------------------

Descriptions

Description	15A 600V FA CLASS RK1 FUSE
extra long description	BUSS KTS-R-15 LIMITRON FAST ACTING
Features	Bussmann's UL Class RK1 fuse offering includes the industry's most recognized Low-Peak dual-element, current-limiting, time-delay fuses (LPN-RK and LPS-RK) which are also available with optional indication on select ratings (see product data sheet). Complementing the Low-Peak product offering is Bussmann's Limitron family of fast-acting fuses (KTN-R, KTS-R, KWN-R and KWS-R) fuses.
Long Description	Eaton Bussmann Series Class RK1 fuse, KTS-R, fast-acting, current limiting fuse, 15 A, rejection style fuse, interrupting rating of 200 kA at 600 Vac
Product Type	Limitron Fast Acting Fuse Class RK1
Special Features	70/30 Brass End Cap



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00051712417044
Manufacturers Part Number	KTS-R-15
UPC	051712417044

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Packaging

Carton	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked