



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1520RW Recp Single WT 20A 250V 3PH 3P4W H/L YI *Eaton Wiring Devices*

Catalog Number	L1520RW
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Watertight Locking Receptacle, #18-10 Awg, 20A, Industrial, 250V, Back Wiring, Yellow, Steel, Single, Watertight, L15-20, Three-Pole, Four-Wire, Thermoplastic, 0.36 to 0.84 In, Ip67
Weight per unit	10.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

dimensions	6.7500 IN X 4.2500 IN X 4.0000 IN
media	Yes

Descriptions

Description	RECP SINGLE WT 20A 250V 3PH 3P4W H/L YL
extra long description	EWD L1520RW Recp Single WT 20A 250V
Features	Eaton's Arrow Hart watertight locking devices utilize a unique, robust design and superior materials to provide watertight security in harsh environments.
Long Description	Eaton Arrow Hart watertight locking receptacle, #18-10 AWG, 20A, Industrial, 250V, Back wiring, Yellow, Steel, Single, Watertight, L15-20, Three-pole, Four-wire, Thermoplastic, 0.36 to 0.84 in, IP67
Product Type	Recp Single WT 20A 250V 3PH 3P4W H/L YI
Special Features	Watertight locking

Manufacturer Information

Brand	Eaton
GTIN	00040893687766
Manufacturers Part Number	L1520RW
UPC	040893687766

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Watertight

Packaging

Carton	1
Package	10
Weight Per each	10



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Facility - OtherCommercial /
Institutional Buildings / Structures - Commercial / Institutional
Buildings / Structures - Other

standard

CSA certified,cULus Listed,NOM,UL Listed,Federal Specifications
Classification W-C375