



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L11.5T848GC840S 11.5W Led T8 48" 40K Ballast Compatible

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | L11.5T848GC840S |
| Manufacturer | Keystone Technologies |
| Description | 11.5W Led T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 4 FT., 4000K, Smartdrive |
| Weight per unit | 0.6500 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|-------------------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | Ballast Dependent |
| ip rating | N/A |
| lumens | 1800 |
| Nominal Length | 36 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 11.5 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | N/A |
| Description | 11.5W LED T8 48" 40K BALLAST COMPATIBLE |
| extra long description | Key KT-LED11.5T8-48GC-840-S-CP 11.5 |
| Long Description | 11.5W LED T8 TUBE, SHATTER-PROOF COATED GLASS, BALLAST COMPATIBLE, 4 FT., 4000K, SMARTDRIVE |
| Product Type | 11.5 W, 1800 Lumen, 4', 220' Beam Angle, Ballast Compatible, |

Manufacturer Information

| | |
|---------------------------|----------------------------|
| Brand | Keystone |
| GTIN | 00890949012925 |
| Manufacturers Part Number | KT-LED11.5T8-48GC-840-S-CP |
| UPC | 890949012925 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|--------|----|
| Carton | 25 |
|--------|----|

| | |
|-----------------|------|
| Weight Per each | 0.65 |
|-----------------|------|

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | Y |
|-------------|---|