



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L17 1/2" L FM7 Conduit Body

Crouse-Hinds

Catalog Number	L17
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 7 Conduit Outlet Body, Feraloy Iron Alloy, L Shape, 1/2"
Weight per unit	N/A
Product Category	Bodies & Covers

Features

dimensions	4.5600 IN X 1.3800 IN X 2.2500 IN
Form	Form 7

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Height	2-1/4
Hub Size	1/2 in
Length	4-9/16
Width	1-3/8

Descriptions

Description	1/2" L FM7 CONDUIT BODY
extra long description	CRS-H L17 1/2 L FORM 7 THRD RIGID O
Features	One hundred years after the introduction of the Condulet, Eaton remains the leader in conduit outlet bodies with its Crouse-Hinds series. The line has grown to six families manufactured in a variety of materials, and Form 7 bodies are offered in 11 different shapes to provide the most flexible offering on the market. Form 7 Condulet outlet bodies approach conduit in size for neat, compact installations. Many shapes and sizes are available for rigid threaded conduit. Our Form 7 family features an exclus
Long Description	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, L shape, 1/2"
Product Type	1/2 L Form 7 THRD Rigid Outlet Body

Manufacturer Information

Brand	Eaton
GTIN	00782274511108
UPC	782274511108



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Conduit outlet body

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D