



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L1430P LKG PLG, 30A 125/250V, Hub Pro, L14-30P

Hubbell Wiring Devices

Catalog Number	L1430P
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Select Spec Twist-Lock®, Commercial/Industrial, Male Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, Black
Weight per unit	0.3500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
connection	Screwed Terminal
Cord Type	All Listed Portables
Current Rating	30
Material	COMPOSITE
Number of Wires	4-Wire Grounding
pallet quantity	3600
Phase	1
Poles	3-Pole
Voltage Rating	125/250
Wattage	7
Wire Size	#12 to #8

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	LKG PLG, 30A 125/250V, HUB PRO, L14-30P
extra long description	HWDK L1430P LKG PLG, 30A 125/250V,
Long Description	Locking Devices, SELECT SPEC Twist-Lock®, Commercial/Industrial, Male Plug, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, Black
Product Type	LKG PLG, 30A 125/250V, Hub Pro, L14-30P
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585840666
Manufacturers Part Number	L1430P
UPC	783585840666



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Male Plug

Packaging

Carton	1
Package	10
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L14-30P
standard	UL/CSA