



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L520CW Conn WT 20A 125V 2P3W LKG YI

*Eaton Wiring Devices*

Catalog Number	L520CW
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Watertight Locking Connector, #18-10 Awg, 20A, Industrial, 125V, Back Wiring, Yellow, Steel, Watertight, L5-20, Two-Pole, Three-Wire, Santoprene Thermoplastic Elastomeric, 0.36 to 0.84 In, Ip67
Weight per unit	10.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

dimensions	6.6100 IN X 4.3700 IN X 3.8700 IN
media	Yes

### Descriptions

Description	CONN WT 20A 125V 2P3W LKG YL
extra long description	EWD L520CW Conn WT 20A 125V 2P3W Lk
Features	Eaton's Arrow Hart watertight locking devices utilize a unique, robust design and superior materials to provide watertight security in harsh environments.
Long Description	Eaton Arrow Hart watertight locking connector, #18-10 AWG, 20A, Industrial, 125V, Back wiring, Yellow, Steel, Watertight, L5-20, Two-pole, Three-wire, Santoprene thermoplastic elastomeric, 0.36 to 0.84 in, IP67
Product Type	Conn WT 20A 125V 2P3W LKG YI
Special Features	Watertight locking

### Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00040893641829
Manufacturers Part Number	L520CW
UPC	040893641829

### Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Watertight

### Packaging

Carton	1
Package	10
Weight Per each	10



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Facility - Other  
Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other

standard

UL Listed, CSA certified, NOM, cULus Listed, RoHS Compliant