



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L27PSHIDE268CSBD 18/22/27W Led Hid Repl 3K/4K/5K Med 2600-3900 LM *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | L27PSHIDE268CSBD |
| Manufacturer | Keystone Technologies |
| Description | 27W, Color & Power Selectable , 27/22/18W, 3K/4K/5K, E26, Directdrive |
| Weight per unit | 0.0525 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 360 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | N/A |
| Nominal Length | N/A |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 27 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | E26 |
| color rendering index (cri) | >80 Deg |
| color temperature | N/A |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | N/A |
| Description | 18/22/27W LED HID REPL 3K/4K/5K MED 2600-3900 LM |
| extra long description | Key KT-LED27PSHID-E26-8CSB-D 27W, C |
| Long Description | 27W, Color & Power Selectable , 27/22/18W, 3k/4k/5k, E26, DirectDrive |
| Product Type | 27W, Color & Power Selectable , 27/22/18W, 3K/4K/5K, E26, Di |

Manufacturer Information

| | |
|---------------------------|--------------------------|
| Brand | Keystone |
| GTIN | 00843654134727 |
| Manufacturers Part Number | KT-LED27PSHID-E26-8CSB-D |
| UPC | 843654134727 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Package 16

Weight Per each 0.0525

Uses, Certifications, and Standards

Energy Star N