



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LAM2A350125 Al Lug 1H 2B 6AWG 1/2" Stud *Panduit Corporation*

Catalog Number	LAM2A350125
Manufacturer	Panduit Corporation
Description	The LAM2A350-12-5 Tin-Plated Aluminum Mechanical Lug, One-Hole, Two Barrel, Is Made From Extruded Aluminum Alloy to Provide Premium Electrical and Mechanical Performance For Wide Wire Range-Taking Capability That Helps Minimize Inventory Requirements. The Plated Steel or Aluminum Set Screw Provides A Durable Electrical Contract Between Conductor and Lug. UL Listed and Csa Certified For Use Up to 600 V and UL Temperature Rated 90 Degrees Celsius.
Weight per unit	0.2760 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	NA
insulation	Non-Insulated
media	Yes
Number of Holes	1
Stud Size	1/2
Voltage Rating	600

Descriptions

Description	AL LUG 1H 2B 6AWG 1/2" STUD
extra long description	PAN LAM2A350-12-5 Pan-Lug™ LAM2A350
Long Description	The LAM2A350-12-5 Tin-Plated Aluminum Mechanical Lug, one-hole, two barrel, is made from extruded aluminum alloy to provide premium electrical and mechanical performance for wide wire range-taking capability that helps minimize inventory requirements. The plated steel or aluminum set screw provides a durable electrical contract between conductor and Lug. UL Listed and CSA Certified for use up to 600 V and UL temperature rated 90 Degrees Celsius.
Product Type	Pan-Lug™ LAM2A350-12-5 Al Mech, 350KCMIL, Tin PLT, 1HOLE, 1/2"ST

Manufacturer Information

Brand	PANDUIT
GTIN	00613056878440
Manufacturers Part Number	LAM2A350-12-5
UPC	613056878440



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description SPLIT BOLTS

Type Mechanical Lug

Packaging

Carton 1

Weight Per each 0.276

Uses, Certifications, and Standards

Application Stranded Aluminum or Copper Code Conductor

Mounting 1.13

standard cULus Listed for use up to 600V & Temperature Rated to 90°C