



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LAM2A600126Y 2BRL Alcu Lug *Panduit Corporation*

Catalog Number	LAM2A600126Y
Manufacturer	Panduit Corporation
Description	The LAM2A600-12-6Y Tin-Plated Aluminum Mechanical Lug, One-Hole, Two Barrel, Is Made From Extruded Aluminum Alloy to Provide Premium Electrical and Mechanical Performance For Wide Wire Range-Taking Capability That Helps Minimize Inventory Requirements. The Plated Steel or Aluminum Set Screw Provides A Durable Electrical Contract Between Conductor and Lug. UL Listed and Csa Certified For Use Up to 600 V and UL Temperature Rated 90 Degrees Celsius.
Weight per unit	3.1 (lbs/each)
Product Category	Large Terminals & Connectors

Features

amperage rating	NA
Material	Tin-Plated Aluminum
media	Yes
Number of Holes	1
Stud Size	1/2
Voltage Rating	600

Descriptions

Description	2BRL ALCU LUG
extra long description	PAN LAM2A600-12-6Y Pan-Lug™ LAM2A60
Long Description	The LAM2A600-12-6Y Tin-Plated Aluminum Mechanical Lug, one-hole, two barrel, is made from extruded aluminum alloy to provide premium electrical and mechanical performance for wide wire range-taking capability that helps minimize inventory requirements. The plated steel or aluminum set screw provides a durable electrical contract between conductor and Lug. UL Listed and CSA Certified for use up to 600 V and UL temperature rated 90 Degrees Celsius.
Product Type	Pan-Lug™ LAM2A600-12-6Y Mech Con-Lugs, 600, Tin PLT Al, STRT

Manufacturer Information

Brand	PANDUIT
GTIN	00074983592708
Manufacturers Part Number	LAM2A600-12-6Y
UPC	074983592708



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Mechanical Lug

Packaging

Carton	1
Package	6
Weight Per each	3.07

Uses, Certifications, and Standards

Application	Stranded Aluminum or Copper Code Conductor
Mounting standard	1.38 UL listed and CSA certified for use up to 600V and UL temperature rated to 90 degrees C