



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3200 N Central Expwy Suite 100
75071-0000, TX Mckinney
Phone: 972-542-1196
Fax: 972-542-2279



L830R R SGL 3W 30A 480V T/L

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | L830R |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlok Registered Single Receptacle, 3-Wire 30A 480V |
| Weight per unit | 0.2322 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|---------|
| amperage rating | 30 |
| indoor/outdoor | Indoor |
| Number of Wires | 3 |
| Outlet Type | Locking |
| Phase | 3 |
| Poles | 2 |
| Voltage | 480.0 V |
| Voltage Rating | 480 |
| Wall Plate Included | NO |
| Wire Size | 14 - 10 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | R SGL 3W 30A 480V T/L |
| extra long description | P&S L830R R SGL 3W30A480V T/L |
| Features | Brass Mounting Strap, Impact Resistant |
| Long Description | Turnlok Registered Single Receptacle, 3-Wire 30A 480V |
| Product Type | R SGL 3W30A480V T/L |
| Special Features | Turnlock, locking device, quick thread assembly, rounded back contour, impact & corrosion resistant, new design external cord grips |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007283051 |
| Manufacturers Part Number | L830-R |
| UPC | 785007283051 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type | RECEPTACLE |

Trade Size

| | |
|----------|------|
| Amperage | 30.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3200 N Central Expwy Suite 100
75071-0000, TX Mckinney
Phone: 972-542-1196
Fax: 972-542-2279

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.2322 |

Uses, Certifications, and Standards

| | |
|-------------|---------------|
| Application | Commercial |
| nema rating | L8-30R |
| standard | CULUS, UL 498 |