



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LAMA500385 Al Mech, 500KCMIL, Tin PLT, 1 Hole, 3/8" Stud *Panduit Corporation*

Catalog Number	LAMA500385
Manufacturer	Panduit Corporation
Description	The LAMA500-38-5 Tin-Plated Aluminum Mechanical Lug, One-Hole, Single Barrel, Is Made From Extruded Aluminum Alloy to Provide Premium Electrical and Mechanical Performance For Wide Wire Range-Taking Capability That Helps Minimize Inventory Requirements. The Plated Steel or Aluminum Set Screw Provides A Durable Electrical Contract Between Conductor and Lug. UL Listed and Csa Certified For Use Up to 600 V and UL Temperature Rated 90 Degrees Celsius.
Weight per unit	1.7 (lbs/each)
Product Category	20240117141652

Features

amperage rating	NA
insulation	Non-Insulated
media	Yes
Number of Holes	1
Stud Size	3/8
Voltage Rating	600

Descriptions

Description	AL MECH,500KCMIL,TIN PLT,1 HOLE,3/8" STUD
extra long description	PAN LAMA500-38-5 Pan-Lug™ LAMA500-3
Long Description	The LAMA500-38-5 Tin-Plated Aluminum Mechanical Lug, one-hole, single barrel, is made from extruded aluminum alloy to provide premium electrical and mechanical performance for wide wire range-taking capability that helps minimize inventory requirements. The plated steel or aluminum set screw provides a durable electrical contract between conductor and Lug. UL Listed and CSA Certified for use up to 600 V and UL temperature rated 90 Degrees Celsius.
Product Type	Pan-Lug™ LAMA500-38-5 Al Mech, 500KCMIL, Tin PLT, 1 Hole, 3/8" S

Manufacturer Information

Brand	PANDUIT
GTIN	00613056878495
Manufacturers Part Number	LAMA500-38-5
UPC	613056878495



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Mechanical Lug

Packaging

Carton	1
Weight Per each	1.66

Uses, Certifications, and Standards

Application	Stranded Aluminum or Copper Code Conductor
standard	UL Listed for use up to 600V & Temperature Rated to 90°C