



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBDG2WH Bridge Lutron

Catalog Number	LBDG2WH
Manufacturer	Lutron
Description	Smart Bridge With Homekit Technology, Allows Control Of Lights and Shades Via The Lutron App or Siri
Weight per unit	0.5500 (lbs/each)
Product Category	Lighting Controls

Features

functions	Remote Link
Material	Plastic
media	Yes
Voltage Rating	5
Wattage	1.3

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Height	1.19
Length	2.75
Width	2.75

Descriptions

Description	BRIDGE
extra long description	LUT L-BDG2-WH Cas ta Wireless Smart
Features	Controlling lights, shades and temperature from a mobile device has never been easier or more reliable. The Lutron Smart hub allows for setup, control, and monitoring of Caseta Wireless dimmers and Serena Remote Controlled Shades from a smartphone, tablet and even your Apple Watch wearable. The Lutron Smart hub works with Alexa, Apple Homekit, Ecobee, the Google Assistant, Ring Honeywell, Logitech, Samsung SmartThings, Sonos, Serena shades & more Use the Smart hub and free app to control lights, shades and
Long Description	Smart Bridge with HomeKit technology, allows control of lights and shades via the Lutron app or Siri
Product Type	Cas Ta Wireless Smart Bridge
Special Features	Supports up to 50 wireless devices. Connects to Wi-fi router via Ethernet. Supports Siri and HomeKit technology, and Serena shades.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00784276099332
Manufacturers Part Number	LBDG2WH
UPC	784276099332

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Smart Bridge

Packaging

Carton	1
Package	18
Weight Per each	0.55

Uses, Certifications, and Standards

Application	Lighting and shade Control
Enclosure	Plastic
Frequency Rating	431 to 437
Mounting standard	Tabletop cUL, NOM, FCC, IC, COFETEL
Temperature Rating	32 to 104