



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LBL100 Laser Level With Bubble Vials, Magnetic

Klein Tools

Catalog Number	LBL100
Manufacturer	Klein Tools
Description	The Klein Tools Laser Line Bubble Level LBL100 Projects A High Power Horizontal Laser Line and Spot Parallel to The Base That Reaches Up to 75-Foot (22.9 M). Use The Laser to Align Ceiling Tiles, Floor Tile, Studs, Wood, Saws, and More. Three Easy to Read Vials Identify Horizontal and Cross At 0-Degree Level and Vertical At 90-Degree. The Strong Rare-Earth Magnets In The Base Of The Level Attach to The Included Leveling Stand and Other Ferromagnetic Surfaces. The Top Features A V-Groove to Fit The Contour
Weight per unit	0.6400 (lbs/each)
Product Category	Tools & Testers

Features

Accuracy	Spot: +/-0.02" (+/-0.5 mm) at 39.4" (1 m) from Level; Vials: 0.043°
included	Batteries; Level; Leveling Stand
Material	Cast Aluminum
media	Yes
Number of Vials	3
Overall Height	1.84" (4.7 cm)
Overall Width	0.85" (2.2 cm)

Dimensions and Weight

Overall Length	7.3" (18.5 cm)
----------------	----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	LASER LEVEL WITH BUBBLE VIALS, MAGNETIC
extra long description	KLEIN LBL100 Laser Line Bubble Leve
Features	The Klein Tools Laser Line Bubble Level LBL100 projects a high power horizontal laser line and spot parallel to the base that reaches up to 75-Foot (22.9 m). Use the laser to align ceiling tiles, floor tile, studs, wood, saws, and more. Three easy to read vials identify horizontal and cross at 0-Degree level and vertical at 90-Degree. The strong Rare-Earth magnets in the base of the level attach to the included leveling stand and other ferromagnetic surfaces. The top features a V-groove to fit the contour
Long Description	The Klein Tools Laser Line Bubble Level LBL100 projects a high power horizontal laser line and spot parallel to the base that reaches up to 75-Foot (22.9 m). Use the laser to align ceiling tiles, floor tile, studs, wood, saws, and more. Three easy to read vials identify horizontal and cross at 0-Degree level and vertical at 90-Degree. The strong Rare-Earth magnets in the base of the level attach to the included leveling stand and other ferromagnetic surfaces. The top features a V-groove to fit the contour
Product Type	Laser Line Bubble Level
Special Features	1/4-20 Threaded Hole for Tripod, Cross Bubble Vial, Leveling Base Included, Magnetic Mounting, V-groove

Manufacturer Information

Brand	Klein Tools
GTIN	00092644692093
Manufacturers Part Number	LBL100
UPC	092644692093

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Laser and Bubble

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	4
Weight	15.6 oz (442 g)
Weight Per each	0.64



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Layout Applications Requiring Level and Plumb Checks
standard	IEC60825-1