



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LBR6AL02SWW1A LBR6 ALO2 SWW1 Ar LSS MWD Mvolt Ugz

*Lithonia Lighting - Acuity*

Catalog Number	LBR6AL02SWW1A
Manufacturer	Lithonia Lighting - Acuity
Description	LBR Is Everything You Need In A Downlight At An Affordable Price. Whether It'S The Seamless Install From-Below Design, Abundant Energy Savings or Maintaining Glare-Free Aesthetics, LBR Is The Perfect Solution For Any Renovation, Remodel or New Construction Project.
Weight per unit	3.7 (lbs/each)
Product Category	Lighting

### Features

average life	60,000
dimensions	1000 LM,1500 LM,2000 LM,Switchable
dimnable	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	1000 LM,1500 LM,2000 LM,Switchable
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Round
Voltage Rating	120-277
Warranty	5
Wattage	25.6

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	80
color temperature	Variable
Finish	Semi-Specular



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	New Construction,Retrofit
Description	LBR6 ALO2 SWW1 AR LSS MWD MVOLT UGZ
extra long description	LITH LBR6 ALO2 SWW1 AR LSS MWD MVOL
Features	Design Select
Long Description	LBR is everything you need in a downlight at an affordable price. Whether it's the seamless install from-below design, abundant energy savings or maintaining glare-free aesthetics, LBR is the perfect solution for any renovation, remodel or new construction project.
Product Type	Retrofit Kit

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00194994846499
Manufacturers Part Number	LBR6 ALO2 SWW1 AR LSS MWD MVOL
UPC	194994846499

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

## Trade Size

aperture size	6 in
---------------	------

## Packaging

Carton	1
Weight	3.688
Weight Per each	3.748

## Uses, Certifications, and Standards

Application	Education,Hospitality,House of Worship,Offices & Banks,Retail,Retrofit
environmental conditions	Indoor
Mounting	Recessed
standard	ULENERGY STAR,Low UGR