



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LCC438DWL 2HL Cu LNG BRL Lug *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | LCC438DWL |
| Manufacturer | Panduit Corporation |
| Description | Long Barrel Lug, #4 Awg (Stranded) Conductor Size, #3 Awg (Stranded);#2 Awg (Solid) Conductor Size, Non-Insulated, Copper Conductor Material, Gray (Code) Insulation Color, +90 °C Operating Temperature, 3.09 In Overall Length, 35 KV, 1 LB/Ea |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|-------------------|
| Material | Tin-Plated Copper |
| media | Yes |
| Number of Holes | 2 |
| Stud Size | 3/8 |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|------|---------------------------------------|
| Size | #4 — #3 AWG Code STR, #2 AWG Code SOL |
|------|---------------------------------------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 2HL CU LNG BRL LUG |
| extra long description | PAN LCC4-38DW-L Pan-Lug™ LCC4-38DW- |

Manufacturer Information

| | |
|-------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983797851 |
| UPC | 074983797851 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Compression Lug |

Packaging

| | |
|-----------------|----|
| Carton | 50 |
| Weight Per each | 1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|----------------------|--|
| Mounting standard | 1-1/8 CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, ABS approved, NEBS Level 3 |
|----------------------|--|