



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LD13T5HE48GC850D *Discontinued* 13W 120-277V 50K T5 Led *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | LD13T5HE48GC850D |
| Manufacturer | Keystone Technologies |
| Description | Linear Fluorescent Led Lamp, Linear, Instant Start Type; 45.19 Inch; UI (Canada and Us), UI, NSF/Ansi, Etl, DLC Approval; Food Equipment Application; 120 to 277 Volt Ac Voltage Rating; 0.82 Inch Diameter |
| Weight per unit | 0.5160 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-------------------|--|
| Beam Spread Angle | 240 Degree |
| Current Rating | 0.11 Amp at 120 Volt AC, 0.05 Amp at 277 Volt AC |
| Glass Finish | FROSTED |
| Intensity | 1800 LUMEN |
| Item | LED Lamp |
| Voltage Rating | 120 to 277 Volt AC |
| Wattage | 13 Watt |

Material, Color, and Finish

| | |
|-----------------------------|--------------------|
| Base Type | G5 Miniature 2-Pin |
| Color Rendering Index | 80 A |
| Color Temperature in Kelvin | 5000 |

Dimensions and Weight

| | |
|----------|------------|
| Diameter | 0.82 INCH |
| Length | 45.19 Inch |

Descriptions

| | |
|------------------------|---|
| Additional Information | RoHS Compliant; Shatter Proof Coated Glass; Efficacy 139 Lumen per Watt; Visible Light Area 325 Degree; Temperature -4 to 113 Deg F |
| Commodity Description | Led Linear Fluorescent Straight, U-Shape & Circular Lamps |
| Description | *DISCONTINUED* 13W 120-277V 50K T5 LED |
| Long Description | LINEAR FLUORESCENT LED LAMP, LINEAR, INSTANT START TYPE; 45.19 INCH; UL (CANADA AND US), UL, NSF/ANSI, ETL, DLC APPROVAL; FOOD EQUIPMENT APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 0.82 INCH DIAMETER |
| Product Type | Linear Fluorescent Led Lamp |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Keystone Technologies |
| Manufacturers Part Number | KT-LED13T5HE-48GC-850-D |
| Model | 800 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
| Type | Linear, Instant Start |

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Weight Per each | 0.516 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Food Equipment |
| Approval | UL (Canada and US), UL, NSF/ANSI, ETL, DLC |