



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED12T848G850S \*Discontinued\* 12W Led T8 48" 50K BLSTD

Keystone Technologies

Catalog Number	LED12T848G850S
Manufacturer	Keystone Technologies
Description	12W Led T8 Lamp, 4FT, 5000K. Smartdrive. Glass Construction. Designed For Use With Instant Start Ballasts Only.
Weight per unit	0.6600 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
lumens	1800
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	12
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### Descriptions

Construction	N/A
Description	*DISCONTINUED* 12W LED T8 48" 50K BLSTD
extra long description	Key KT-LED12T8-48G-850-S /G2-CP 12W
Long Description	12W LED T8 LAMP, 4FT, 5000K. SMARTDRIVE. GLASS CONSTRUCTION. DESIGNED FOR USE WITH INSTANT START BALLASTS ONLY.
Product Type	12W, 1800 Lumen, 4', 220' Beam Angle, Ballast Compatible, DL

### Manufacturer Information

Brand	Keystone
GTIN	00890949016725
Manufacturers Part Number	KT-LED12T8-48G-850-S /G2-CP
UPC	890949016725



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
--------	----

Weight Per each	0.66
-----------------	------

## Uses, Certifications, and Standards

Energy Star	Y
-------------	---