



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED13T848G835X3 13W Led T8 48" 35K Combo Glass 1800LM *Keystone Technologies*

| | |
|------------------|--|
| Catalog Number | LED13T848G835X3 |
| Manufacturer | Keystone Technologies |
| Description | 13W T8 Led Tube, Ballast Compatible & 120-277V Line Voltage Compatible (Single or Double Ended Wiring) 4FT, 3500K, Combodrive X3 |
| Weight per unit | 0.6600 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|-------------------------------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V OR Ballast Dependent |
| ip rating | N/A |
| lumens | 2000 |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 13 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 3500 |
| housing color | N/A |

Descriptions

| | |
|------------------------|--|
| Construction | Frosted Glass |
| Description | 13W LED T8 48" 35K COMBO GLASS 1800LM |
| extra long description | Key KT-LED13T8-48G-835-X3 13W, 1800 |
| Long Description | 13W T8 LED Tube, Ballast Compatible & 120-277V Line Voltage Compatible (Single OR Double Ended Wiring) 4ft, 3500K, ComboDrive X3 |
| Product Type | 13W, 1800 Lumen, 4' , 220' Beam Angle, Glass Construction, S |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Keystone |
| GTIN | 00843654129440 |
| Manufacturers Part Number | KT-LED13T8-48G-835-X3 |
| UPC | 843654129440 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.66 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|