



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED13T848G8CSJX3 13W Led T8 48" 3K/35K/4K/5K/65K Combo Tube Glass

Keystone Technologies

Catalog Number	LED13T848G8CSJX3
Manufacturer	Keystone Technologies
Description	13W Led T8 Tube, 2000 Lumen, Glass Construction, 4FT, Color Select 3000/3500/4000/5000K/6500K, Ballast Compatible & 120-277V Line Voltage Compatible (Single or Double Ended Wiring), Combo Drive X3
Weight per unit	0.0272 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V OR Ballast Dependent
ip rating	N/A
lumens	2000
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	13
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	N/A
housing color	N/A

### Descriptions

Construction	Frosted Glass
Description	13W LED T8 48" 3K/35K/4K/5K/65K COMBO TUBE GLASS
extra long description	Key KT-LED13T8-48G-8CSJ-X3 13W LED
Long Description	13W LED T8 Tube, 2000 lumen, Glass Construction, 4ft, Color Select 3000/3500/4000/5000K/6500k, Ballast Compatible & 120-277V Line Voltage Compatible (Single OR Double Ended Wiring), Combo Drive X3
Product Type	13W Led T8 Tube, 2000 Lumen, Glass Construction, 4FT, Color



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654156149
Manufacturers Part Number	KT-LED13T8-48G-8CSJ-X3
UPC	843654156149

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	25
Weight Per each	0.0272

## Uses, Certifications, and Standards

Energy Star	N
-------------	---