



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LED15T8U6GC840S 15W Led T8 Ubend 40K Coated Type A 2000LM

*Keystone Technologies*

Catalog Number	LED15T8U6GC840S
Manufacturer	Keystone Technologies
Description	15W Led T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 6" U-Bend, 4000K, 12 PCS Carton, Carton Pack
Weight per unit	1.0 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
lumens	2200
Nominal Length	6 in U-Bend
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	15
Wire Type	N/A

### Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

### Descriptions

Construction	Frosted Shatterproof Glass
Description	15W LED T8 UBEND 40K COATED TYPE A 2000LM
extra long description	Key KT-LED15T8-U6GC-840-S-CP 15W, 2
Long Description	15W LED T8 Tube, Shatter-Proof Coated Glass, Ballast Compatible, 6" U-Bend, 4000K, 12 pcs Carton, Carton Pack
Product Type	15W, 2000 Lumen, 4', 240' Beam Angle, Ballast Compatible, DL

### Manufacturer Information

Brand	Keystone
GTIN	00890949013410
Manufacturers Part Number	KT-LED15T8-U6GC-840-S-CP
UPC	890949013410



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

## Packaging

Carton	12
--------	----

Weight Per each	1.03
-----------------	------

## Uses, Certifications, and Standards

Energy Star	N
-------------	---